

# ***IRONskin***<sup>®</sup>



## **Examination Gloves**

Non Sterile - Ambidextrous - Disposable

Powdered & Powder Free



Protective Examination Gloves From ***IRONskin***<sup>®</sup>

Examination gloves you can rely on during diagnosis, handling instruments and medical procedures.

The perfect way to prevent infection from patients with contagious diseases through their body fluids or physical contact.

Tested & proved safe against dermal sensitization & skin irritation

Confirms to ASTM D 3578 Quality Standards

ISO 9001 guidelines followed in production

Using CE approved absorbable corn starch, USP grade

No 29 & 31, Jalan Indah 2/16, Taman Universiti Indah,  
43300 Seri Kembangan, Selangor, Malaysia.

Tel : 603-8942 8007 / 603-8940 8152

Fax : 603-8942 3007

[www.gloveresources.com](http://www.gloveresources.com)



**Glove Resources Sdn Bhd**  
( 769201 - X )

## Lightly Powdered Examination Gloves

Dimension Properties	Glove Size	Palm Width(mm)	Overall Length(mm)
	Extra Small (XS)	75 ± 5	235 ± 5
	Small (S)	85 ± 5	235 ± 5
	Medium (M)	95 ± 5	235 ± 5
	Large (L)	110 ± 5	235 ± 5
	Extra Large (XL)	120 ± 5	235 ± 5

  

Pre-Shipment Inspection	Inspection Criteria	Inspection Level	AQL
	Freedom from holes	G-1	1.5
	Visual Inspection for major defects	S-4	2.5
	Visual Inspection for minor defects	S-4	4.0
	Dimensions	S-2	4.0
	Physical Properties	S-2	4.0



Thickness	Thickness Measurements(mm)	Single Wall(mm)
	Finger	0.15 ± 0.03
	Palm	0.12 ± 0.03
	Cuff	0.10 ± 0.03

Physical Properties	Glove Properties	Before Aging	After Aging
	Tensile Strength(Mpa)	21 min.	14 min.
	Ultimate Elongation(%)	700 min.	500 min.
	Force at Break(N)	7.5 min.	5.5 min.

## Powder Free Latex Examination Gloves

Dimension Properties	Glove Size	Palm Width(mm)	Overall Length(mm)
	Extra Small (XS)	75 ± 5	235 ± 5
	Small (S)	85 ± 5	235 ± 5
	Medium (M)	95 ± 5	235 ± 5
	Large (L)	110 ± 5	235 ± 5
	Extra Large (XL)	120 ± 5	235 ± 5

  

Pre-Shipment Inspection	Inspection Criteria	Inspection Level	AQL
	Freedom from holes	G-1	1.5
	Visual Inspection for major defects	S-4	2.5
	Visual Inspection for minor defects	S-4	4.0
	Dimensions	S-2	4.0
	Physical Properties	S-2	4.0



Thickness	Thickness Measurements(mm)	Single Wall(mm)
	Finger	0.15 ± 0.03
	Palm	0.12 ± 0.03
	Cuff	0.10 ± 0.03

Physical Properties	Glove Properties	Before Aging	After Aging
	Tensile Strength(Mpa)	21 min.	14 min.
	Ultimate Elongation(%)	700 min.	500 min.
	Force at Break(N)	7.5 min.	5.5 min.

## Powder Free Nitrile Examination Gloves

Dimension Properties	Glove Size	Palm Width(mm)	Overall Length(mm)
	Extra Small (XS)	75 ± 5	235 ± 5
	Small (S)	85 ± 5	235 ± 5
	Medium (M)	95 ± 5	235 ± 5
	Large (L)	110 ± 5	235 ± 5
	Extra Large (XL)	120 ± 5	235 ± 5

  

Pre-Shipment Inspection	Inspection Criteria	Inspection Level	AQL
	Freedom from holes	G-1	1.5
	Visual Inspection for major defects	S-4	2.5
	Visual Inspection for minor defects	S-4	4.0
	Dimensions	S-4	4.0
	Physical Properties	S-4	4.0



Thickness	Thickness Measurements(mm)	Single Wall(mm)
	Finger	0.15 ± 0.03
	Palm	0.12 ± 0.03
	Cuff	0.10 ± 0.03

Physical Properties	Glove Properties	Before Aging	After Aging
	Tensile Strength(Mpa)	16 min.	14 min.
	Ultimate Elongation(%)	600 min.	500 min.
	Force at Break(N)	6 min.	5.5 min.

